



Backer Rod

No. 6917

PRODUCT DESCRIPTION

Basic Uses: QUIKRETE® Backer Rod is an ideal non-absorbent compressible backup material. It is inserted into a joint to

- control sealant depth
- to create a backstop
- Allow proper sealant tooling
- Allow proper sealant wetting of the joint surfaces

It can also be used as a temporary seal.

QUIKRETE® Backer Rod may be used for:

- Expansion joints
- Curtain wall joints
- Partitions
- Log construction
- Pavement joints
- Pre-cast units

Compatibility: QUIKRETE® Backer Rod is ideal for use with QUIKRETE® Polyurethane Non-Sag Sealant (no. 8660-11) or QUIKRETE® Polyurethane Self-Leveling Sealant (no. 8660-10) but it is compatible with any butyl, polysulfide, acrylic, polyurethane, silicone and most other cold applied sealant compositions. QUIKRETE® Backer Rod is an extruded round, closed cell, low density polyethylene foam material with a skin-like outer texture. It is highly flexible and compressible for easy installation. QUIKRETE® Backer Rod is chemically inert and will resist oil, gasoline and most other solvents. This material will not stain nor adhere to sealant materials and is non-exuding (see Table 1 for physical properties).

Sizes: QUIKRETE® Backer Rod is packaged in 20 ft (6.1 m) lengths. Available in 1" (25 mm) and 3/4" (19 mm) diameter.


TECHNICAL DATA

The typical physical properties of QUIKRETE® Backer Rod are listed in Table 1.

Table 1: Physical Properties

Density (ASTM D 1622)	2.0 lb/cu.ft. (32 kg/M ³)
Tensile Strength (ASTM D 1623)	50 PSI (0.34 MPa)
Compression Deflection (ASTM D 1621)	5 PSI (3.4 kPa) @ 25%
Water Absorption (ASTM C 509)	0.02% by volume
Water Absorption (ASTM C 1016)	0.03 g / mL

Figure 1: TYPICAL APPLICATION:



INSTALLATION:

Joint or opening must be clean, dry and free of obstructions. Select backer rod diameter from Table 2. Cut backer rod to length and use a blunt instrument or roller to uniformly install backer rod so that the sealant depth will be about 1/2 of the joint width. **DO NOT PUNCTURE, STRETCH OR OVERLY COMPRESS.**

Table 2: Size Selection

Joint Width	Backer Rod Diameter
3/8" to 1/2" (9 to 12 mm)	3/4" (19 mm)
5/8" to 3/4" (15 to 19 mm)	1" (25 mm)

Fill the joint with an appropriate sealant and allow it to cure. QUIKRETE® Polyurethane

The QUIKRETE® Companies, Inc.

One Securities Centre
3490 Piedmont Road, Suite 1300
Atlanta, GA 30305
404.634.9100

Non-Sag Sealant (no. 8660-11) is recommended for vertical expansion joints but can also be used for horizontal expansion joints. **QUIKRETE® Polyurethane Self-Leveling Sealant (no. 8660-10)** is ideal for horizontal joints.

Warranty

The QUIKRETE® Companies warrant this product to be of merchantable quality when used or applied in accordance with the instructions or applied in accordance with the instructions herein. The product is not warranted as suitable for any purpose or use other than the general purpose for which it is intended. Liability under this warranty is limited to the replacement of its product (as purchased) found to be defective, or at the shipping companies' option, to refund the purchase price. In the event of a claim under this warranty, notice must be given to The QUIKRETE® Companies in writing at Atlanta, GA 30305. The limited warranty is issued and accepted in lieu of all other express warranties and expressly excludes liability for consequential damages.

The QUIKRETE® Companies, Inc.

One Securities Centre
3490 Piedmont Road, Suite 1300
Atlanta, GA 30305
404.634.9100